
INSTALLATION INSTRUCTIONS

EXTENSION COLUMNS

CMA-0305 to CMA-18024 

The CMA-0305 through the CMA-18024 extension columns can be used with any NPT 1 1/2" coupler to lower your mount to the desired height. The extension columns are divided into 2' ranges, each providing vertical adjustments in 1" increments. The column tube telescopes and bolts through at the desired height.

WARNING: IMPROPER INSTALLATION MAY RESULT IN SERIOUS PERSONAL INJURY!

All components must be securely fastened to a structural member capable of supporting five times the combined weight of all components plus the equipment being mounted. If it cannot support this weight, the structure **MUST** be reinforced.

The maximum weight to be installed on the column is 500 pounds (226.8 Kg).



Unpack and check contents:

- (1) Extension Pipe
- (1) Adjuster Tube
- (1) 3/8-16 x 2 1/2" Bolt

- (1) 3/8-16 Nylock Nut
- (2) 5/16" Set Screws
- (1) 5/32" Allen Wrench

INSTALLATION INSTRUCTIONS

1. Slide adjuster tube into extension pipe to desired length, matching holes in adjuster tube with extension pipe.
2. Secure adjuster tube to extension pipe using 3/8-16 x 2 1/2" bolt and 3/8-16 Nylock nut.
3. Install both 5/16" set screws in holes of extension tube on each side of 3/8-16 x 2 1/2" bolt.

WARNING! ALWAYS THREAD EXTENSION PIPE AND ADJUSTER TUBE AT LEAST 6 OR 7 FULL TURNS INTO MATING SURFACES.



CHIEF MANUFACTURING INC.
1-800-582-6480 952-894-6280 FAX 952-894-6918
12800 HIGHWAY 13 SOUTH, SUITE 500
SAVAGE, MINNESOTA 55378 USA

2003 Chief Manufacturing
www.chiefmfg.com
01/03