



**SMA-600
MOUNTING PLATE
FOR THE SMART-LIFT 150 AND SMART-LIFT 236**

The SMA-600 mounting plate allows you to attach the Smart-Lift (model SL-150 and SL-236) to a 1½” NPT threaded pipe (compatible with CMA-100 and CMA-110) for suspended ceiling mounting applications.

Unpack carton and check contents:

- | | | | |
|-----|--|------|----------------------------|
| (1) | Mounting Plate | (8) | 3/8 Washers |
| (1) | Top Mounting Plate | (4) | 3/8 - 16 Nut |
| (1) | Bottom Mounting Plate | (1) | 5/16 - 18 Socket Set Screw |
| (4) | 5/16 - 18 Flange Nut | (1) | 5/32 Allen Wrench |
| (4) | 3/8-16 X 3 1/2” Tap Bolt (SL-236 only) | (10) | 8-32 X 1/2” Screw |

CAUTION!!! The overhead support must be capable of supporting five times the weight of the mount and equipment combined. If it cannot, it MUST be reinforced.

INSTALLATION INSTRUCTIONS

1. Attach bottom mounting plate, through mounting plate, to top mounting plate and secure using four 5/16-18 flange nuts on protruding studs of the bottom mounting plate (see picture).
2. Open Smart-Lift (refer to Smart-Lift Instructions).
3. Insert four 3/8– 16 X 3 ½” bolts and washers in holes in top of Smart Lift.
4. Secure mounting plate to Smart Lift using four 3/8 – 16 nuts and washers.
5. *See Smart-Lift installation instructions.*

